

PRISM

Thanks to its highly durable PC frame, the PRISM model offers excellent protection as well as great value for money.



22 g



1614401 • Clear Lens



1614402 • Smoke Lens



1614403 • Silver Flash Lens



1614404 • Bronze Lens








1614406 • Amber Lens

- + ULTRA LIGHT WEIGHT & RIMLESS POLYCARBONATE FRAME**
- + SINGLE PIECE 8 BASE, DISTORTION FREE LENS**
- + FULLY RECYCLABLE: ALL POLYCARBONATE FRAME WITH NO METAL PARTS**

bollé
SAFETY

PRISM

MODEL	VERSIONS	PRODUCT CODE	LENS MARKING	FRAME MARKING	COATINGS
PRISM	 Clear	1614401	IO	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog
	 Smoke	1614402	I3	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog
	 Silver Flash	1614403	I2	AS/NZS 1337.1.2010	Hard coat
	 Bronze	1614404	I3	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog
	 Amber	1614406	IO	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog

LENS MARKING

- I. The letter 'I' signifies 'Medium Impact' approval.
- O. The letter 'O' marking signifies that the product has been approved for the use both outdoors and indoors and the terminology used by Australian standards is 'outdoor un-tinted'. This marking appears on all clear, amber and contrast lenses

OCULAR LENS CATEGORY:

- O. Range of luminous transmittance 80-100% (clear & amber).
- 2. Range of luminous transmittance 18-43% (flash).
- 3. Range of luminous transmittance 8 -18% (smoke & bronze).

APPLICATIONS

- Driving
- Solar UV exposure
- Emergency response
- Rigging
- Assembly and production work

MAIN MARKETS

- Manufacturing
- Petrochemical
- Construction
- Government
- Mining
- Medical and dental
- Food industry

LENSES

- 2mm polycarbonate
- 8 base curve
- 'ALS' anti-fog/anti-scratch coating on both sides of lens: Clear, Smoke, Bronze and Amber
- Hard coating on Silver Flash lens
- 100% UV 385 – Clear
- 100% UV 400 – Smoke, Silver Flash, Bronze and Amber

CLEANING AND STORAGE

CLEANING : Bollé Safety recommends only using our **BOLLÉ CLEAN** Lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: Store between 5 and 40 °, humidity <90%.

CHARACTERISTICS

LENSES	PC - 2,2 mm - Curve 8
FRAME	PC
TEMPLES	PC
STRAP	Non applicable
FOAM	Non applicable
SPARE LENSES	No

FRAME MARKING

AS/NZS 1337.1.2010 : Tested and approved to AS/NZS 1337.1.2010 for medium impact protection. Resists a 6mm at 45 m/s.

ASIA/PACIFIC HEADQUARTERS :

Bollé Australia Pty Ltd
32-40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: safety@bolle.com.au

NEW ZEALAND:

Bollé New Zealand Limited
Unit 5, 114 Sawyers Arms Road
Papanui, Christchurch 8052
T: 03 3751400
E: bolle@bolle.co.nz